

Seat shell chassis Galileo for e-driving systems

REHATEC®

Cost estimate

Address / Billing address


Order

Delivery address

Purchaser

Date

Order name



If a conversion is carried out later due to subsequent approval of the power drive, additional conversion costs will be incurred.

Figure does not correspond to the base model | Dimensional tolerances $\pm 3\%$

Base model

- Welded abduction frame
- Seat plate adjustable in depth
- Wheel camber 0° and 2°
- Seat tilting up to 40°
- Manual backrest recline adjustment up to 35°
- Back can be folded down and is steplessly adjustable in depth
- Castor wheels with aluminium castor forks and castor stems
- Drive wheels with push rims, drum brake carriers and hand brake levers
- Push bar

Hilfsmittelnummer

mit Greifreifen

26.99.01.1067



Crash tested
according to
ISO 7176-19

This wheelchair
frame complies
with ISO 7176-19,
transporting users
in motor vehicles
(with wheelchair-
tiedown and
occupant-restraint
system).

Weight and load capacity

Weight:

depending on your configuration at
least 13.5 kg

Load capacity:

Max. load capacity
(Patient's weight incl. seat shell)
Up to 79 kg: with standard frame
From 80 kg to 120 kg:
with closed frame and double gas
spring

Please consider these facts!

Weitere technische Daten finden Sie auf www.rehatec.com -> Downloads. Oder fordern Sie diese einfach per eMail, FAX oder Post an!

Preise gültig bis auf Widerruf ab 01.01.2026. Preise zzgl. ges. MwSt. © Vervielfältigung nur mit Genehmigung der Rehatec GmbH erlaubt.

Technische Änderungen vorbehalten. Es gelten unsere Allgemeinen Geschäftsbedingungen. Diese finden Sie auf www.rehatec.com.

Mit einer Bestellung bestätigen Sie automatisch unsere AGB gelesen und akzeptiert zu haben.

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, Tel. (06228) 9136-0, Fax. (06228) 9136-99, info@rehatec.com, www.rehatec.com


Seite 1

01.01.26

1024063_5

Technical Data

Galileo seat shell mobility base for power drives



Size tolerance of $\pm 3\%$ | More seat heights available on request!

Seat heights scalamobil (f)

Size Mini – 2k			Size 2l – 6		
20"	22"	24"	20"	22"	24"
42,5 – 45 cm	42,5 – 47,5 cm	44,5 – 49,5 cm	44,5 – 47 cm	44,5 – 49,5 cm	47 – 52 cm

Seat heights e-fix (f)

Size Mini – 2k		Size 2l – 6	
22"	24"	22"	24"
42,5 cm	44,5 cm	44,5 cm	46,5 cm

Seat heights viamobil (f)

Size Mini – 2k			Size 2l – 6		
20"	22"	24"	20"	22"	24"
42,5 – 45 cm	42,5 – 47 cm	44,5 – 49,5 cm	44,5 – 47 cm	44,5 – 49,5 cm	47 – 52 cm

Seat heights e-motion (f)

Size Mini – 2k		Size 2l – 6	
22"	24"	22"	24"
42,5 – 47,5 cm	44,5 – 49,5 cm	44,5 – 49,5 cm	47 – 52 cm

Measurements

Size	(a) Total length	(b) Total width ⁽¹⁾	(c) Seat plate - back depth ⁽²⁾		Seat plate width	(d) Seat plate depth	
			Standard seat plate	Extended seat plate		Standard	Extended
Mini	70 - 84 cm	54 cm	29,5 - 32,5 cm	35 - 38 cm	20,5 cm	26,5 cm	32 cm
0	70 - 84 cm	57 cm	29,5 - 32,5 cm	35 - 38 cm	20,5 cm	26,5 cm	32 cm
1	70 - 84 cm	60 cm	35 - 38 cm	41 - 48 cm	26,5 cm	32 cm	38 cm
2 short	70 - 84 cm	63 cm	35 - 38 cm	41 - 48 cm	26,5 cm	32 cm	38 cm
2 long	78 - 93 cm	63 cm	35 - 38 cm	41 - 48 cm	26,5 cm	32 cm	38 cm
3	78 - 93 cm	66 cm	41 - 48 cm	46 - 53 cm	32,5 cm	38 cm	43 cm
4	78 - 93 cm	69 cm	41 - 48 cm	46 - 53 cm	32,5 cm	38 cm	43 cm
5	78 - 93 cm	72 cm	46 - 53 cm	—	38,5 cm	43 cm	—
6	78 - 93 cm	75 cm	46 - 53 cm	—	38,5 cm	43 cm	—

⁽¹⁾ The total width is reduced by 3 cm when applying a wheel camber of 0 degrees. ⁽²⁾ From the seat plate's front edge to the back

Size	(e) Knee angle extension from seat plate	(g) Seat plate - back height	(h) Width between drive wheels ⁽³⁾		Frame length	(i) Inner frame width	Back recline
			Wheel guards incl.	No wheel guards			
Mini	bis 4 cm	58 - 67 cm	32,5 cm	34,5 cm	58 cm	29,5 cm	35°
0	bis 4 cm	58 - 67 cm	35,5 cm	37,5 cm	58 cm	32,5 cm	35°
1	bis 4 cm	58 - 67 cm	38,5 cm	40,5 cm	58 cm	35,5 cm	35°
2 short	bis 6,5 cm	58 - 67 cm	41,5 cm	43,5 cm	58 cm	38,5 cm	35°
2 long	bis 6,5 cm	58 - 67 cm	41,5 cm	43,5 cm	68 cm	38,5 cm	35°
3	bis 6,5 cm	58 - 67 cm	44,5 cm	46,5 cm	68 cm	41,5 cm	35°
4	bis 6,5 cm	58 - 67 cm	47,5 cm	49,5 cm	68 cm	44,5 cm	35°
5	bis 6,5 cm	58 - 67 cm	50,5 cm	52,5 cm	68 cm	47,5 cm	35°
6	bis 6,5 cm	58 - 67 cm	53,5 cm	55,5 cm	68 cm	50,5 cm	35°

⁽³⁾ The distance between the drive wheels extends by 3 cm when applying a wheel camber of 0 degrees (referring to 22" drive wheels). Assuming 20" drive wheels, the distance between the drive wheels extends by 0.5 cm (3.5 cm in total) and assuming 24" drive wheels, the distance is reduced by 0.5 cm (2.5 cm in total).

Weitere technische Daten finden Sie auf www.rehatec.com -> Downloads. Oder fordern Sie diese einfach per eMail, FAX oder Post an!

Preise gültig bis auf Widerruf ab 01.01.2026. Preise zzgl. ges. MwSt. © Vervielfältigung nur mit Genehmigung der Rehatec GmbH erlaubt.

Technische Änderungen vorbehalten. Es gelten unsere Allgemeinen Geschäftsbedingungen. Diese finden Sie auf www.rehatec.com.

Mit einer Bestellung bestätigen Sie automatisch unsere AGB gelesen und akzeptiert zu haben.

Rehatec GmbH, In den Kreuzwiesen 35, 69250 Schönau, Tel. (06228) 9136-0, Fax. (06228) 9136-99, info@rehatec.com, www.rehatec.com

ATTENTION! Installation or retrofitting only possible by AAT!

E-accessories									
Power drives	Mini	0	1	2 short	2 long	3	4	5	6
V-MAX	X	X	X	WAK	WAK	WAK	WAK	WAK	WAK
V-MAX ²	X	X	X	WAK	WAK	WAK	WAK	WAK	WAK
MAX-E	X	X	X	WAK	WAK	WAK	WAK	WAK	WAK
s-max	X	X	X	VAK	VAK	VAK	VAK	VAK	VAK
CAMILINO	X	X	X	VAK	VAK	VAK	VAK	VAK	VAK
SOLO	VKR	VKR	VKR	VKR	VKR	VKR	VKR	VKR	VKR
SERVO	VKR	VKR	VKR	VKR	VKR	VKR	VKR	VKR	VKR

The V-MAX mini push assist is not compatible with the Galileo seat shell mobility base!

X = Installation not possible; V = Installation possible with 24" W = Installation possible with 20" and 24";

R = Only Rehatec anti-tip devices possible; K = Installation possible with Kraftknotensystem; A = Only AAT anti-tip device possible

Frame size / Compatibility											
	Mini/0/1	2K/2L		3		4		5		6	
Wheel size	24"	20"	24"	20"	24"	20"	24"	20"	24"	20"	24"
V-MAX	X	V/O/K/R/A		V/O/K/R/A		V/O/K/R/A		V/O/K/R/A		V/O/K/R/A	
V-MAX ²	X										
MAX-E	X										
s-max	X	X	C/K/A/R	X	C/K/A/R	X	C/K/A/R	X	C/K/A/R	X	C/K/A/R
CAMILINO	X	X	C/K/A/R	X	C/K/A/R	X	C/K/A/R	X	C/K/A/R	X	C/K/A/R
SOLO	S/K/R/A	X	S/K/R/A	X	S/K/R/A	X	S/K/R/A	X	S/K/R/A	X	S/K/R/A
SERVO	S/K/R/A	X	S/K/R/A	X	S/K/R/A	X	S/K/R/A	X	S/K/R/A	X	S/K/R/A

X = Installation not possible

0 = Installation only possible with 0° camber frame version

V = Overall length increases by 16 cm! Overall width increases by 4 cm! The distance between the drive wheels increases by 4 cm! The maximum seat depth corresponds to min. seat plate-back depth + 3 cm. Installation only possible with wheelbase extension (1021179), long brake handle (1015588) and widened parking brakes (1013170). These parts are only available from AAT!

C = Overall width increases by 3.5 cm! DThe maximum seat depth corresponds to min. seat plate-back depth + 3 cm! A seat pan tilt is not possible with this power drive! Installation only possible with wheel guard option (1017672 / 1017684)!

S = Overall width increases by 6 cm! The distance between the drive wheels increases by 3 cm! If wheel guards and anti-tip devices are required, installation only possible with wheelguard (1017672 / 1017684) and Rehatec anti-tip devices!

K = Rehatec Kraftknotensystem option possible

R = Rehatec anti-tip devices possible

A = AAT anti-tip devices possible

R = Rehatec anti-tip devices not possible!

A = AAT anti-tip devices not possible!

The Rehatec tipping bar and medical platform options are not possible with these power drives.

ATTENTION!

Planned combinations with power drives as well as with the s-max must be coordinated with AAT **before preparing the cost estimate! **

This overview has been prepared with the utmost care. Nevertheless, errors cannot be completely ruled out. Rehatec® accepts no liability in such cases.

For further information, please contact AAT Antriebstechnik directly (www.aat-online.de).

Weitere technische Daten finden Sie auf www.rehatec.com -> Downloads. Oder fordern Sie diese einfach per eMail, FAX oder Post an!

Preise gültig bis auf Widerruf ab 01.01.2026. Preise zzgl. ges. MwSt. © Vervielfältigung nur mit Genehmigung der Rehatec GmbH erlaubt.

Technische Änderungen vorbehalten. Es gelten unsere Allgemeinen Geschäftsbedingungen. Diese finden Sie auf www.rehatec.com.

Mit einer Bestellung bestätigen Sie automatisch unsere AGB gelesen und akzeptiert zu haben.

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, Tel. (06228) 9136-0, Fax. (06228) 9136-99, info@rehatec.com, www.rehatec.com

Kompatible E-Antriebe

Electronic driving system	Type <i>please specify</i>	Mini	0	1	2 short	2 long	3	4	5	6
scalamobil	S30 S35	—	—	✓	✓	✓	✓	✓	✓	✓
viamobil	V15 V25	—	—	—	✓	✓	✓	✓	✓	✓
<i>Eco-Variation not possible</i>										
scala- und viamobil		—	—	—	—	—	—	✓	✓	✓
e-fix	E35 E36	✓	✓	✓	✓	✓	✓	✓	✓	✓
e-motion	M15	✓	M15	✓	✓	✓	✓	✓	✓	✓
via GO (1)	—	—	—	✓	✓	✓	✓	✓	✓	✓

Its not possible to assemble the tipping bar of Rehatec® for scalamobil and viamobil!

The assembly of the anti-tip-device for the wheelchair restrain system or the support loops of Rehatec® and the anti-tip-device of Alber is possible for every electronic driving system.

(1) The combination with the via GO push assist is generally possible from size 1 onwards!

For further details, please refer to the DIP (Dealer Information Pool) at <https://dip.alber.de/home.html>


scalamobil (S30/S35)

Size	Seat plate – back depth (c) (page 2)		Drive wheel size	User weight
	Standard seat plate	Extended seat plate		
Mini	—	—	—	—
0	—	—	—	—
1	35 – 38 cm	41 – 45 cm	12" + 16", 20" – 24"	bis 60 kg
2 short	35 – 38 cm	41 – 45 cm	12" + 16", 20" – 24"	bis 60 kg
2 long	35 – 38 cm	41 – 45 cm	12" + 16", 20" – 24"	bis 60 kg
3	41 – 45 cm	46 – 50 cm	12" + 16", 20" – 24"	bis 60 kg
4	41 – 45 cm	46 – 50 cm	12" + 16", 20" – 24"	bis 90 kg (2)
5	46 – 50 cm	—	12" + 16", 20" – 24"	bis 120 kg
6	46 – 50 cm	—	12" + 16", 20" – 24"	bis 120 kg

When configuring a Galileo size 1–3 with Scalamobil and Kraftknottensystem, the seat tilt is limited (maximum 18° possible).

With 16" wheels and Scalamobil, the Kraftknottensystem is not possible!

Only from 20" possible!




(2) Mit doppelter Gasdruckfeder bis zu 120 kg

viamobil (V15/V25)


Size	Seat plate – back depth (c) (page 2)		Drive wheel size
	Standard seat plate	Extended seat plate	
Mini	—	—	—
0	—	—	—
1	—	—	—
2 short	35 – 38 cm	41 – 45 cm	12" + 16", 20" – 24"
2 long	35 – 38 cm	41 – 45 cm	12" + 16", 20" – 24"
3	41 – 45 cm	46 – 50 cm	12" + 16", 20" – 24"
4	41 – 45 cm	46 – 50 cm	12" + 16", 20" – 24"
5	46 – 50 cm	—	12" + 16", 20" – 24"
6	46 – 50 cm	—	12" + 16", 20" – 24"

ATTENTION!
The seat tilt is only possible up to a maximum of 10° as standard! Drive wheels only available from 20"!




e-Fix (E35 / E36)

Size	Seat plate – back depth (c) (page 2)		Drive wheel size	Total width	Width between drive wheels (h)	
	Standard seat plate	Extended seat plate			with wheel guard	without wheel guard
Mini	29,5 – 32,5 cm	35 – 38 cm	22" – 24"	54 cm	31 cm	33 cm
0	29,5 – 32,5 cm	35 – 38 cm	22" – 24"	57 cm	33 cm	36 cm
1	35 – 38 cm	41 – 48 cm	22" – 24"	60 cm	37 cm	39 cm
2k	35 – 38 cm	41 – 48 cm	22" – 24"	63 cm	40 cm	42 cm
2l	35 – 38 cm	41 – 48 cm	22" – 24"	63 cm	40 cm	42 cm
3	41 – 48 cm	46 – 53 cm	22" – 24"	66 cm	43 cm	45 cm
4	41 – 48 cm	46 – 53 cm	22" – 24"	69 cm	46 cm	48 cm
5	46 – 53 cm	—	22" – 24"	72 cm	49 cm	51 cm
6	46 – 53 cm	—	22" – 24"	75 cm	52 cm	54 cm



e-motion (M15)

Size	Seat plate – back depth (c) (page 2)		Drive wheel size	Total width
	Standard seat plate	Extended seat plate		
Mini	29,5 – 32,5 cm	35 – 38 cm	22" – 24"	54 cm
0	29,5 – 32,5 cm	35 – 38 cm	22" – 24"	57 cm
1	35 – 38 cm	41 – 48 cm	22" – 24"	60 cm
2 short	35 – 38 cm	41 – 48 cm	22" – 24"	63 cm
2 long	35 – 38 cm	41 – 48 cm	22" – 24"	63 cm
3	41 – 48 cm	46 – 53 cm	22" – 24"	66 cm
4	41 – 48 cm	46 – 53 cm	22" – 24"	69 cm
5	46 – 53 cm	—	22" – 24"	72 cm
6	46 – 53 cm	—	22" – 24"	75 cm




Weitere technische Daten finden Sie auf www.rehatec.com -> Downloads. Oder fordern Sie diese einfach per eMail, FAX oder Post an!

Preise gültig bis auf Widerruf ab 01.01.2026. Preise zzgl. ges. MwSt. © Vervielfältigung nur mit Genehmigung der Rehatec GmbH erlaubt.

Technische Änderungen vorbehalten. Es gelten unsere Allgemeinen Geschäftsbedingungen. Diese finden Sie auf www.rehatec.com.

Mit einer Bestellung bestätigen Sie automatisch unsere AGB gelesen und akzeptiert zu haben.

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, Tel. (06228) 9136-0, Fax. (06228) 9136-99, info@rehatec.com, www.rehatec.com



Push assist EMPULSE R20

Size	Zeile	Possible position for wheel axle when clamps are mounted on the frame (P1)			Possible position for wheel axle when clamps are mounted on the frame (P2)		
		20 inch	22 inch	24 inch	20 inch	22 inch	24 inch
Mini	A	—	—	—	—	—	—
	B						
	C						
0	A	1, 2, 3, 4, 5	—	2, 3, 4, 5	—	—	—
	B						
	C						
1	A	1, 2, 3, 4, 5	—	2, 3, 4, 5	—	—	—
	B						
	C						
2	A	—	—	2, 3, 4, 5	—	1, 2, 3	1, 2, 3
	B					1, 2, 3	1, 2, 3
	C					1, 2, 3	1, 2, 3
3	A	2, 3, 4, 5	2, 3, 4, 5	2, 3, 4, 5	1, 2, 3	1, 2, 3	1, 2, 3
	B				1, 2, 3	1, 2, 3	1, 2, 3
	C				1, 2, 3	1, 2, 3	1, 2, 3
4	A	—	—	3, 4, 5	1, 2	1, 2, 3	1, 2, 3, 4
	B				1, 2, 3	1, 2, 3, 4	1-5
	C				1, 2, 3, 4	1-5	1, 2, 3, 4
5	A	3, 4, 5	3, 4, 5	1, 2, 3	1-5	—	1, 2, 3, 4
	B				1, 2, 3, 4	1, 2, 3, 4	1, 2, 3, 4
	C				1, 2, 3, 4	1, 2, 3, 4	1, 2, 3, 4
6	A	3, 4, 5	3, 4, 5	1, 2, 3	1-5	—	1, 2, 3, 4
	B				1, 2, 3, 4	1, 2, 3, 4	1, 2, 3, 4
	C				1, 2, 3, 4	1, 2, 3, 4	1, 2, 3, 4



This overview has been prepared with the utmost care.
Nevertheless, errors cannot be completely ruled out.
Rehatec® accepts no liability in such cases.
For further information, please contact Sunrise Medical directly
(www.sunrisemedical.de)

Weitere technische Daten finden Sie auf www.rehatec.com -> Downloads. Oder fordern Sie diese einfach per eMail, FAX oder Post an!

Preise gültig bis auf Widerruf ab 01.01.2026. Preise zzgl. ges. MwSt. © Vervielfältigung nur mit Genehmigung der Rehatec GmbH erlaubt.

Technische Änderungen vorbehalten. Es gelten unsere Allgemeinen Geschäftsbedingungen. Diese finden Sie auf www.rehatec.com.

Mit einer Bestellung bestätigen Sie automatisch unsere AGB gelesen und akzeptiert zu haben.

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, Tel. (06228) 9136-0, Fax. (06228) 9136-99, info@rehatec.com, www.rehatec.com

Base frame

Galileo seat shell mobility base for power drives

REHATEC®

CAUTION! Please consider wheel camber!

Standard frame, abducted		2° wheel camber	Closed frame, abducted											
Single gas spring Total load up to 79 kg	Double gas spring Total load up to 79 kg	Double gas spring Total load up to 79 kg	Double gas spring (required when 80 kg are exceeded!)Total load up to 120 kg											
Size Mini (1015911) Size 0 (1015912) Size 1 (1015913) Size 2 short (1015810) Size 2 long(1015919) Size 3 (1015920) Size 4 (1016462)	Size 3 (1015917) Size 4 (1015918) Size 5 (1015827) Closed frame with double gas spring required from 80 kg upwards! Specify total load! <table><tr><td>Total load</td><td>Gas spring</td></tr><tr><td>up to 79 kg</td><td>2 × 200 N</td></tr></table>	Total load	Gas spring	up to 79 kg	2 × 200 N	Size 2 long(1017182) Size 3 (1017251) Size 4 (1017252) Closed frame with double gas spring required from 80 kg upwards! Specify total load!	Size 3 (1017253) Size 4 (1017254) Size 5 (1017255) Size 6 (1017800) Indicate total load! <table><tr><td>Total load</td><td>Gas spring</td></tr><tr><td>up to 79 kg</td><td>2 × 200 N (1)</td></tr><tr><td>exceeding 80 kg</td><td>2 × 350 N (1)</td></tr></table>		Total load	Gas spring	up to 79 kg	2 × 200 N (1)	exceeding 80 kg	2 × 350 N (1)
Total load	Gas spring													
up to 79 kg	2 × 200 N													
Total load	Gas spring													
up to 79 kg	2 × 200 N (1)													
exceeding 80 kg	2 × 350 N (1)													
Base price	Base price	Base price	Base price											

⁽¹⁾ In case you do not specify the total load, we apply 2 x 200 N by default.

Standard frame, abducted			0° wheel camber	Closed frame, abducted								
Single gas spring Total load up to 79 kg		Double gas spring Total load up to 79 kg		Double gas spring Total load up to 79 kg		Double gas spring (required when 80 kg are exceeded!) Total load up to 120 kg						
Size Mini (1018668)		Size 3 (1018675)		Size 2 long(1018683)		Size 3 (1018686)						
Size 0 (1018669)		Size 4 (1018676)		Size 3 (1018684)		Size 4 (1018687)						
Size 1 (1018670)		Size 5 (1018677)		Size 4 (1018685)		Size 5 (1018688)						
Size 2 short (1018671)		Closed frame with double gas spring required from 80 kg upwards! Specify total load!		Closed frame with double gas spring required from 80 kg upwards! Specify total load!		Size 6 (1018689)						
Size 2 long(1018672)						Indicate total load!						
Size 3 (1018673)						<table><tr><td>Total load</td><td>Gas spring</td></tr><tr><td>up to 79 kg</td><td>2 × 200 N (1)</td></tr><tr><td>exceeding 80 kg</td><td>2 × 350 N (1)</td></tr></table>	Total load	Gas spring	up to 79 kg	2 × 200 N (1)	exceeding 80 kg	2 × 350 N (1)
Total load	Gas spring											
up to 79 kg	2 × 200 N (1)											
exceeding 80 kg	2 × 350 N (1)											
Size 4 (1018674)												

⁽¹⁾ In case you do not specify the total load, we apply 2 x 200 N by default.

Frame colours

 Pure white (RAL 9010)	 Bordeaux violet (RAL 4004)	 Luminous green (RAL 6038)
 Daffodil yellow (RAL 1007)	 Ultramarine blue (RAL 5002)	 Anthracite grey, matt (RAL 7016m)
 Luminous yellow (RAL 1026)	 Metallic traffic blue*	 Metallic silver*
 Pure orange (RAL 2004)	 Pearl night blue, matt (RAL 5026)	 Metallic anthracite*
 Luminous orange (RAL 2005)	 Water blue (RAL 5021)	 Graphite black, matt (RAL 9011m)
 Ruby red (RAL 3003)	 Light green (RAL 6027)	 Glossy jet black (RAL 9005g)
 Pearl ruby red, matt (RAL 3032)	 Yellow green (RAL 6018)	
 Heather violet (RAL 4003)	 Pearl green, matt (RAL 6035)	

* keine RAL Farben

This is only an overview of colours. Find all details at www.rehatec.com.

Patient's muscle tone

Stereotypic movements
(e.g. permanent body rocking)*

Measurements

Seath shell width	Seat shell depth
cm	cm

Total load (patient+seat shell)

kg

* Please check whether any customisations, such as reinforcements of the base frame, are required due to stereotypical behaviour! Requirements can be specified under "Notes" on the last page!

Weitere technische Daten finden Sie auf www.rehatec.com -> Downloads. Oder fordern Sie diese einfach per eMail, FAX oder Post an!

Preise gültig bis auf Widerruf ab 01.01.2026. Preise zzgl. ges. MwSt. © Vervielfältigung nur mit Genehmigung der Rehatec GmbH erlaubt.

Technische Änderungen vorbehalten. Es gelten unsere Allgemeinen Geschäftsbedingungen. Diese finden Sie auf www.rehatec.com.

Mit einer Bestellung bestätigen Sie automatisch unsere AGB gelesen und akzeptiert zu haben.

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, Tel. (06228) 9136-0, Fax. (06228) 9136-99, info@rehatec.com, www.rehatec.com

Seite 6

01.01.26

1024063_5

Wheels, backrest and armrests

REHATEC®

Galileo seat shell mobility base for power drives


Drive wheels including drum brake															
Caution! Mountainbike and Big Apple wheels extend Galileo's total width by 4 cm!		Standard version 		Mountainbike Code 4063 Off-road tyres 		Big Apple Code 4068 Wide tyres for increased contact area 		Marathon Code 4080 (22") Code 4074 (24") Narrow tyres, shallow tread 							
				Pair		Pair		369, – €		Pair		369, – €		Pair/extra charge	
		12"	16"	20"	22"	24"	24"		24"		22"		24"		
Solid rubber	Grey	—	—				—		—		—		—		
	Black		(3)				—		—		—		—		
Pneumatic	Grey	—	—				—		—		—		—		
	Black														


(3) Surcharge 177,- € (Code 4059)

Possible combinations					
	12"	16"	20"	22"	24"
5"	✓	✓	✓	✓	✓
6"	✓	✓	✓	✓	✓
7"	✓	✓	✓	✓	✓
8"	⚠ (4)	✓	⚠ (4)	✓	✓



(4) Only with extension kit for castor wheels



Castor wheels					
		5"	6"	7"	8"
Solid rubber	Grey				
	Black				
Pneumatic	Grey	—			
	Black	—			

Push bar	
Push bar, height- and angle-adjustable Code 1024683 	
Stück	170,- €

Push rims		
Push rims, anodised aluminium Sturdy, high-quality push rims, width-adjustable		
		
Only compatible with standard rims (pneumatic, solid rubber, and Marathon tyres)!		
Size	colour	Code
20"	black	1025482-S
22"	silver	1025388-N
24"	black	1025389-S
Mounting: tight (standard) wide		
Paar	80,- €	

Configuration		Colour of the back	Brake handle locking	Tilt-in-space	Seat plate
Mounting of the parking brake	Standard	Standard	Standard	Standard	Standard
	 Graphite black, matt	 Graphite black, matt	Automatic	0° to 40°	Standard
			optional	optional	optional
			Manual	-5° to 35°	Extended

Back	
Back fastening with split, fixed bracket Code 1016485 	
Not to be combined with back element!	
Each	290,- €
Back fastening with split, adjustable bracket Code 1017928 	
Not to be combined with back element! For perfect guidance of the back section	
Each	327,- €

Arm rests																									
Arm rests, standard Code 1017771			Arm rests, comfort Code 1017437																						
Height-, width- and angle-adjustable by toothed segments			Height-, width- and angle-adjustable by clamping system, foldable backwards by 95°																						
		<table><thead><tr><th>Size</th><th>(b) Distance between the arm rests</th></tr></thead><tbody><tr><td>Mini/0</td><td>19 - 35 cm</td></tr><tr><td>1/2</td><td>24 - 39 cm</td></tr><tr><td>3/4</td><td>30 - 45 cm</td></tr><tr><td>5/6</td><td>36 - 51 cm</td></tr></tbody></table>	Size	(b) Distance between the arm rests	Mini/0	19 - 35 cm	1/2	24 - 39 cm	3/4	30 - 45 cm	5/6	36 - 51 cm			<table><thead><tr><th>Size</th><th>(b) Distance between the arm rests</th></tr></thead><tbody><tr><td>Mini/0</td><td>25 - 42 cm</td></tr><tr><td>1/2</td><td>31 - 46 cm</td></tr><tr><td>3/4</td><td>37 - 52 cm</td></tr><tr><td>5/6</td><td>43 - 58 cm</td></tr></tbody></table>	Size	(b) Distance between the arm rests	Mini/0	25 - 42 cm	1/2	31 - 46 cm	3/4	37 - 52 cm	5/6	43 - 58 cm
Size	(b) Distance between the arm rests																								
Mini/0	19 - 35 cm																								
1/2	24 - 39 cm																								
3/4	30 - 45 cm																								
5/6	36 - 51 cm																								
Size	(b) Distance between the arm rests																								
Mini/0	25 - 42 cm																								
1/2	31 - 46 cm																								
3/4	37 - 52 cm																								
5/6	43 - 58 cm																								
Paar		Please select one	350,- €	Paar																					
				Please select one																					
				513,- €																					

Weitere technische Daten finden Sie auf www.rehatec.com -> Downloads. Oder fordern Sie diese einfach per eMail, FAX oder Post an!

Preise gültig bis auf Widerruf ab 01.01.2026. Preise zzgl. ges. MwSt. © Vervielfältigung nur mit Genehmigung der Rehatec GmbH erlaubt.

Technische Änderungen vorbehalten. Es gelten unsere Allgemeinen Geschäftsbedingungen. Diese finden Sie auf www.rehatec.com.

Mit einer Bestellung bestätigen Sie automatisch unsere AGB gelesen und akzeptiert zu haben.

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, Tel. (06228) 9136-0, Fax. (06228) 9136-99, info@rehatec.com, www.rehatec.com



Seite 7


01.01.26




1024063_5

Backrest and frame

Galileo seat shell mobility base for power drives

Back			
Back adjustment via gas spring Code 362 For an easy adjustment of the back recline		Dynamic back adjustment Code 1021386 Dynamic back via gas spring Adjustable from 0° to 95° Fixable 350 N 700 N	
Each		124, – €	
Each(customisation)		501, – €	
			One-hand operation of the seat tilting via double gas spring Code 1020332 Release handle releases double gas spring (Code 1000862) Only available for seat tilt adjustment via double gas spring
Each			65, – €


Lower back section made to measure Code 5192 for maximum seat tilt in combination with a viamobil V15 / V25 Only possible from size 2 onwards	Back extension by 13 cm Code 1026520 Only available for sizes 5 and 6 and in combination with a push bar! Height adjustment by extension tubes not applicable.	
Each(customisation) 372, – €	Each(customisation) 266, – €	

Frame									
Extension kit for castor wheels Distance between castor wheels extends by 6 cm.	 horizontal Seat height remains the same.								
 diagonal Seat height increases.	 diagonal Seat height decreases.								
<table border="1"> <thead> <tr> <th>Code</th><th></th></tr> </thead> <tbody> <tr> <td>1016879</td><td>Diagonal version Seat height increases by 4 cm</td></tr> <tr> <td>1016879</td><td>Diagonal version Seat height decreases by 4 cm</td></tr> <tr> <td>1017876</td><td>Horizontal version</td></tr> </tbody> </table>	Code		1016879	Diagonal version Seat height increases by 4 cm	1016879	Diagonal version Seat height decreases by 4 cm	1017876	Horizontal version	Not to be combined with steering device, push aid and castor wheel stop.
Code									
1016879	Diagonal version Seat height increases by 4 cm								
1016879	Diagonal version Seat height decreases by 4 cm								
1017876	Horizontal version								
Pair	203, – €								

Rahmen, Adapter und Sicherheit



REHATEC®

Galileo seat shell mobility base for power drives



Frame		Bracket for scala / viamobil		Installation of the power drive bracket by REHATEC® Code 4005																
Wheel base extension Code 1021179 Extended by 6 to 11 cm  Not to be combined with scala-/viamobil, 12/16" wheels, tipping bar, tipping bar for vent tray or the extension kit for drive wheels!		<table><thead><tr><th>Size</th><th>scalamobil Code</th><th>viamobil Code</th></tr></thead><tbody><tr><td>1</td><td rowspan="3">1591745</td><td>—</td></tr><tr><td>2 short</td><td rowspan="2">1591742</td></tr><tr><td>2 long</td></tr><tr><td>3</td><td rowspan="4">1591770</td><td>1591746</td></tr><tr><td>4</td></tr><tr><td>5</td></tr><tr><td>6</td></tr></tbody></table>		Size	scalamobil Code	viamobil Code	1	1591745	—	2 short	1591742	2 long	3	1591770	1591746	4	5	6	Not eligible for discount!	
Size	scalamobil Code	viamobil Code																		
1	1591745	—																		
2 short		1591742																		
2 long																				
3	1591770	1591746																		
4																				
5																				
6																				
Pair	442, – €	Each	362, – €	Each	89, – €															

The brackets for e-fix and e-motion, as well as all other accessories (bolts, etc.) for your power drive, must be ordered directly from Alber GmbH.



Seat shell adapter		Trapezoidal adapter, lower part																																					
Trapezoidal adapter, complete⁽²⁾ <table border="1"> <thead> <tr> <th>For size</th><th>Code</th><th>a</th><th>b</th></tr> </thead> <tbody> <tr> <td>Mini-0</td><td>1020031</td><td>20 cm</td><td>21 cm</td></tr> </tbody> </table> <table border="1"> <thead> <tr> <th>For size</th><th>Code</th><th>c</th><th>d</th></tr> </thead> <tbody> <tr> <td>1-2</td><td>1008603</td><td>24 cm</td><td>25 cm</td></tr> <tr> <td>3-6</td><td>1008589</td><td>30 cm</td><td>28 cm</td></tr> </tbody> </table> 		For size	Code	a	b	Mini-0	1020031	20 cm	21 cm	For size	Code	c	d	1-2	1008603	24 cm	25 cm	3-6	1008589	30 cm	28 cm	 <table border="1"> <thead> <tr> <th>For size</th><th>Code</th><th>a</th><th>b</th></tr> </thead> <tbody> <tr> <td>Mini-0</td><td>1016878</td><td>20 cm</td><td>21 cm</td></tr> <tr> <td>1-2</td><td>1011358</td><td>24 cm</td><td>25 cm</td></tr> <tr> <td>3-6</td><td>1011356</td><td>30 cm</td><td>28 cm</td></tr> </tbody> </table>		For size	Code	a	b	Mini-0	1016878	20 cm	21 cm	1-2	1011358	24 cm	25 cm	3-6	1011356	30 cm	28 cm
For size	Code	a	b																																				
Mini-0	1020031	20 cm	21 cm																																				
For size	Code	c	d																																				
1-2	1008603	24 cm	25 cm																																				
3-6	1008589	30 cm	28 cm																																				
For size	Code	a	b																																				
Mini-0	1016878	20 cm	21 cm																																				
1-2	1011358	24 cm	25 cm																																				
3-6	1011356	30 cm	28 cm																																				
Each	438, – €	Each	230, – €																																				

⁽²⁾ Sizes Mini and 0 include pin instead of lever.

Safety		Scalamobil anti-tip device without lifting function with 12 mm mount	
Tipping bar Code 1003725  Not possible with scala / viamobil.		Anti-tip Code 1016245  Only possible in combination with scala / viamobil bracket! Not eligible for discount!	
Left	93, – €	Left	161, – €
Right	93, – €	Right	161, – €
		Pair (customisation)	865, – €

Weitere technische Daten finden Sie auf www.rehatec.com -> Downloads. Oder fordern Sie diese einfach per eMail, FAX oder Post an!

Preise gültig bis auf Widerruf ab 01.01.2026. Preise zzgl. ges. MwSt. © Vervielfältigung nur mit Genehmigung der Rehatec GmbH erlaubt.

Technische Änderungen vorbehalten. Es gelten unsere Allgemeinen Geschäftsbedingungen. Diese finden Sie auf www.rehatec.com.


Mit einer Bestellung bestätigen Sie automatisch unsere AGB gelesen und akzeptiert zu haben.




Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, Tel. (06228) 9136-0, Fax. (06228) 9136-99, info@rehatec.com, www.rehatec.com

Seite 9

01.01.26

1024063_5

Safety															
Castor wheel stop Code 1026240			Wheel guard Code 360												
															
<table><tr><td>4"</td><td>5"</td><td>6"</td><td>7"</td><td>8"</td></tr><tr><td>—</td><td>—</td><td>—</td><td>✓</td><td>✓</td></tr></table>			4"	5"	6"	7"	8"	—	—	—	✓	✓	Farbe: Graphitschwarz matt (RAL 9011m)		
4"	5"	6"	7"	8"											
—	—	—	✓	✓											
Nicht kombinierbar mit Lenk- und Schiebehilfe sowie mit Verbreiterungssatz für Lenkräder!			Not possible for e-motion!												
Pair			Pair												
229, – €			248, – €												

Spoke guards, transparent  <table><tr><th>Für</th><th>Code</th></tr><tr><td>20"</td><td>1013997</td></tr><tr><td>22"</td><td>1014001</td></tr><tr><td>24"</td><td>1014006</td></tr></table><table><tr><td>12"</td><td>16"</td><td>20"</td><td>22"</td><td>24"</td></tr><tr><td>—</td><td>—</td><td>✓</td><td>✓</td><td>✓</td></tr></table>	Für	Code	20"	1013997	22"	1014001	24"	1014006	12"	16"	20"	22"	24"	—	—	✓	✓	✓	Parking brake/knee lever brake at the drive wheel Code 1016486  Bracket colour: Graphite black, matt (RAL 9011m)	Parking brake with extension handle Code 1011637 Extension of the brake lever by 5.5 cm 
Für	Code																			
20"	1013997																			
22"	1014001																			
24"	1014006																			
12"	16"	20"	22"	24"																
—	—	✓	✓	✓																
Pair225, – €	Pair183, – €	Pair61, – €																		

restraint system* Code 299-1 For a safe transport in a motor vehicle when the patient is sitting in the mobility base Lashing rings incl. a pelvic restraint belt adjustable in length (590 / 1225 mm) Bei Anpassungen/ Sonderbauten ist die Verwendung von einem Kraftknotensystem grundsätzlich nicht möglich! Dies kann nur durch eine Einzelfallprüfung entschieden werden! Available at Rehatec only!	Lashing rings for transport in motor vehicles Code 1017933-1 For a safe transport in a motor vehicle when the patient is not sitting in the mobility base 4 lashing rings (2 × in the front / 2 × in the back) without pelvic restraint belt	Installation of the restraint system at REHATEC® Code 4005 When ordered without "installation by Rehatec", several parts of the product must be disassembled and reassembled. Not eligible for discount!
Each(customisation)	Each(customisation)	Each
568, – €	381, – €	89, – €

* **ACHTUNG:** Das Sitzschalenfahrgestell Galileo ist nur mit dem Rehatec-eigenen Kraftknotensystem nach ISO 7176-19 crashgetestet und für den Transport in Kraftfahrzeugen zugelassen! Für etwaige Kraftknotensysteme von Fremdherstellern übernimmt Rehatec daher keine Haftung!

Weitere technische Daten finden Sie auf www.rehatec.com -> Downloads. Oder fordern Sie diese einfach per eMail, FAX oder Post an!

Preise gültig bis auf Widerruf ab 01.01.2026. Preise zzgl. ges. MwSt. © Vervielfältigung nur mit Genehmigung der Rehatec GmbH erlaubt.

Technische Änderungen vorbehalten. Es gelten unsere Allgemeinen Geschäftsbedingungen. Diese finden Sie auf www.rehatec.com.

Mit einer Bestellung bestätigen Sie automatisch unsere AGB gelesen und akzeptiert zu haben.

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, Tel. (06228) 9136-0, Fax. (06228) 9136-99, info@rehatec.com, www.rehatec.com

Swing-up Leg Positioning

Galileo seat shell mobility base for power drives

REHATEC®

Swing-up foot supports, standard

Swing-up parted foot rests, standard


Code 1019503

Adjustable in width and depth

Swing-away, removable and (mechanical) swing-up foot rests

Foot rest mounting incl.

Only optional height adjustment for the foot rest enables the adjustment of the height of physiological pivot point.



Available for Galileo size 2 and bigger!


a (leg length)	b (knee angle)	c (pivot point - seat plate distance)
36–58 cm	85°	11 cm

Foot rests, plastic

Code 1019439

Parted swing-up foot rest, angle-adjustable by 360°

For size	a	b
2	16 cm	14 cm
3–4	16 cm	16 cm
5–6	16 cm	18,5 cm



Base price

557, – €


Accessories for swing-up foot supports, standard

Fußplatten Aluminium

Code 1018565

Parted swing-up foot rest, angle-adjustable by 360°

For size	a	b
2	16 cm	13,5 cm
3	16 cm	15 cm
4	24 cm	16,5 cm
5+6	24 cm	18 cm
5+6	24 cm	21 cm



Footplates 24x21 cm only available from a seat shell width of 47 cm!


Pair

191, – €

Foot rest height adjustment

Code 1017760

To adjust the physiological pivot point



Pair


118, – €

Calf pad with swing-away bracket

Code 1019467

Vertically adjustable, adapts to the user's calf

For size	a	b
2–3	15 cm	12 cm
4–6	21 cm	15 cm




Pair

158, – €

Heel edge (heel strap)

Code 1019442

Mounted on plastic foot rests. Enclosed when you order aluminium foot rests.



Pair

78, – €

Swing-up foot supports, special

Swing-up parted foot rests, special


Code 1018558

Adjustable in width, depth and height (foot rest height adjustment)

Swing-away, removable and swing-up (via gas spring)

Foot rest mounting incl.

Adjustable physiological pivot point




Available for Galileo size 2 and bigger! Intended for spastic users!

a (Leg length)	b (Knee angle)	c (pivot point - seat plate distance)
36–58 cm	80°	15,5–25,5 cm

Foot rests, plastic

Code 1019439

Parted swing-up foot rest, angle-adjustable by 360°




For size	a	b
2	16 cm	14 cm
3+4	16 cm	16 cm
5+6	16 cm	18,5 cm

Foot rests, aluminium

Code 1018565

Parted swing-up foot rest, angle-adjustable by 360°



For size	a	b
2	16 cm	13,5 cm
3	16 cm	15 cm
4	24 cm	16,5 cm
5+6	24 cm	18 cm
5+6	24 cm	21 cm

Footplates 24x21 cm only available from a seat shell width of 47 cm!


Plastic

Aluminium^(*)

Foot rest height adjustment

Code 1017760

To adjust the physiological pivot point




Calf pad with swing-away bracket

Code 1019467

Vertically adjustable, adapts to the user's calf

For size	a	b
2–3	15 cm	12 cm
4–6	21 cm	15 cm



Base price (Pair, customisation)


994, – €

Accessories for swing-up foot supports, special

Fersenkante (Fersenband)

Code 1019442

Mounted on plastic foot rests. Enclosed when you order aluminium foot rests.



Pair

78, – €

^(*) If nothing is selected, this option will be supplied.

Weitere technische Daten finden Sie auf www.rehatec.com -> Downloads. Oder fordern Sie diese einfach per eMail, FAX oder Post an!

Preise gültig bis auf Widerruf ab 01.01.2026. Preise zzgl. ges. MwSt. © Vervielfältigung nur mit Genehmigung der Rehatec GmbH erlaubt.

Technische Änderungen vorbehalten. Es gelten unsere Allgemeinen Geschäftsbedingungen. Diese finden Sie auf www.rehatec.com.

Mit einer Bestellung bestätigen Sie automatisch unsere AGB gelesen und akzeptiert zu haben.

Rehatec GmbH, In den Kreuzwiesen 35, 69250 Schönau, Tel. (06228) 9136-0, Fax. (06228) 9136-99, info@rehatec.com, www.rehatec.com

Leg Positioning

Galileo seat shell mobility base for power drives


REHATEC®

Leg positioning

Light-weight footplate

Fixed knee angle with footplate mounting

Aluminium knee angle and footplate



Only for size Mini to size 2!


19 cm deep (Code 1016648)

268, – €

Footplate

Adjustable knee angle, fixed foot angle with footplate mounting

Steel knee angle, aluminium footplate




Footboard only available from size 1!
24 cm only available from size 2!

16 cm deep, for size 1 and bigger (Code 213)
24 cm deep, for size 2 and bigger (Code 213.24)

336, – €
388, – €

Footplate, parted

Adjustable knee angle, fixed foot angle with mounting. Knee angle made of steel, footboard made of aluminium.




Footboard only available from size 1!
24 cm only available from size 2!

16 cm deep, for size 1 and bigger (Code 21301)
24 cm deep, for size 2 and bigger (Code 21301.24)

415, – €
468, – €

Footboard mounting for third-party footboard




Code	for Size	
1007282	Mini-0	15 × 15 mm
1011252	1-6	20 × 20 mm inkl. 15 × 15 mm Einleger

Pair

124, – €

Adjustable foot angle

Code 214




Not to be combined with folding mechanism and light-weight footplate.

Pair/ Extra charge

121, – €

Folding mechanism -22° up to 90°

Code 1017724




Not to be combined with folding mechanism and light-weight footplate.

Pair/ Extra charge

189, – €

Heel loop

Not to be combined with light-weight footplate.



Code	Footboard	Quantity
217-1	for continuous footboard	Piece
217-2	for split footboard	Pair


Piece/ Pair

121, – €

Calf support

Not available for lightweight footboard.

Code	For size	a	b
1010801		11 cm	28 cm
1010802	1-6	11 cm	31 cm
1010803		16 cm	33 cm
1010804	2-6	16 cm	36 cm
1010805	4-6	16 cm	39 cm




Each

206, – €

Calf supports, parted

Not available for light-weight footboard.

Code	For size	a	b	c
1010835	1-6	11 cm	12,5 cm	26,5 cm
1010837		11 cm	15 cm	31 cm
1010314	2-6	16 cm	18 cm	37,5 cm



Pair

256, – €

Weitere technische Daten finden Sie auf www.rehatec.com -> Downloads. Oder fordern Sie diese einfach per eMail, FAX oder Post an!

Preise gültig bis auf Widerruf ab 01.01.2026. Preise zzgl. ges. MwSt. © Vervielfältigung nur mit Genehmigung der Rehatec GmbH erlaubt.

Technische Änderungen vorbehalten. Es gelten unsere Allgemeinen Geschäftsbedingungen. Diese finden Sie auf www.rehatec.com.

Mit einer Bestellung bestätigen Sie automatisch unsere AGB gelesen und akzeptiert zu haben.

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, Tel. (06228) 9136-0, Fax. (06228) 9136-99, info@rehatec.com, www.rehatec.com

Seite 12

01.01.26

1024063_5

Seating system


Seat element without connecting hinge

Code 1017923

Colour: graphite black, matt (RAL 9011m)

Nicht mit Rückenlehnen in einem Treppenzug kombinieren!

Size	a (depth)	b (width)
Mini	34–39 cm	25–30 cm
0	34–38 cm	28–30 cm
1	34–38 cm	31–36 cm
2	40–47 cm	34–39 cm
3	40–47 cm	37–43 cm
4	45–53 cm	40–46 cm
5	45–53 cm	43–50 cm




Back element without connecting hinge

Code 1017924

Colour: graphite black, matt (RAL 9011m)

For size	a (back height)		b (width)	
Mini	35 cm	40 cm		26 cm
0	35 cm	40 cm	45 cm	29 cm
1	40 cm	45 cm	50 cm	32 cm
2	45 cm	50 cm	55 cm	35 cm
3	45 cm	50 cm	55 cm	38 cm
4	50 cm	55 cm	60 cm	41 cm
5	50 cm	55 cm	60 cm	44 cm



Not to be combined with back fastening systems for seat shells!

Each

237, – €


Each

388, – €

Connecting hinge


Code 1017925

To stabilise the seat element and back element, abducted.
To be combined with seat element and back element.



Pair

Seat element extension towards the back



Size	Code
Mini–0	1018300
1–2I	1018297
3–4	1018301
5	1018302


Each

Sitzsystem

Universal bracket to mount the headrest at the back

Code 1009420


When ordered without back element, the universal bracket is supplied loose.



Headrest, shell-shaped

Code 60013

Size	a	b
0	13 cm	22 cm
1	16 cm	28 cm
2	20 cm	33 cm
3	23 cm	38 cm



Each

50, – €

Each

259, – €

For any customisations, please use the 'Modifications/Customisations' form sheet available at www.rehatec.com under 'Downloads'.

Please consider that the prices of spare parts might differ from the prices specified in this order form.