

Galileo Mobility Base for e-driving systems

REHATEC®

Cost estimate

Address / Billing address


Order

Delivery address

Purchaser

Date

Order name



If a conversion is carried out later due to subsequent approval of the power drive, additional conversion costs will be incurred.

Figure does not correspond to the base model | Dimensional tolerances $\pm 3\%$

Base model

- Welded abduction frame
- Seat plate adjustable in depth
- Wheel camber 0° and 2°
- Seat tilting up to 40°
- Manual backrest recline adjustment up to 35°
- Back can be folded down and is steplessly adjustable in depth
- Castor wheels with aluminium castor forks and castor stems
- Drive wheels with push rims, drum brakes and hand brake
- Angel-adjustable push handles

Reimbursement code Germany

with grab handles **26.99.01.1067**



Crash tested
according to
ISO 7176-19

This wheelchair frame complies with ISO 7176-19, transporting users in motor vehicles (with wheelchair-tiedown and occupant-restraint system).

Weight and load capacity

Weight:

depending on configuration at least from 13.5 kg

Load capacity:

Max. load capacity

(Patient's weight incl. seat shell)

Up to 79 kg: with standard frame

From 80 kg to 120 kg:

with closed frame and double gas spring

Please consider this when placing your order!


Additional technical details available at www.rehatec.com -> Downloads. Or send us your request by email, fax or letter.

Valid from 01.01.2026 until recalled. © Unauthorized duplication without prior permission of Rehatec GmbH is strictly prohibited.

Technical changes reserved. Our general terms and conditions apply, see www.rehatec.com.

By ordering our products, you confirm that you have read and accepted our general terms and conditions

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, T: +49 6228 9136-0, F: +49 6228 9136-99, info@rehatec.com, www.rehatec.com



Size tolerance of $\pm 3\%$ | More seat heights available on request!

Seat heights scalamobil (f)

| Size Mini – 2k | | | Size 2l – 6 | | |
|----------------|----------------|----------------|--------------|----------------|------------|
| 20" | 22" | 24" | 20" | 22" | 24" |
| 42,5 – 45 cm | 42,5 – 47,5 cm | 44,5 – 49,5 cm | 44,5 – 47 cm | 44,5 – 49,5 cm | 47 – 52 cm |

Seat heights e-fix (f)

| Size Mini – 2k | | Size 2l – 6 | |
|----------------|---------|-------------|---------|
| 22" | 24" | 22" | 24" |
| 42,5 cm | 44,5 cm | 44,5 cm | 46,5 cm |

Seat heights viamobil (f)

| Size Mini – 2k | | | Size 2l – 6 | | |
|----------------|--------------|----------------|--------------|----------------|------------|
| 20" | 22" | 24" | 20" | 22" | 24" |
| 42,5 – 45 cm | 42,5 – 47 cm | 44,5 – 49,5 cm | 44,5 – 47 cm | 44,5 – 49,5 cm | 47 – 52 cm |

Seat heights e-motion (f)

| Size Mini – 2k | | Size 2l – 6 | |
|----------------|----------------|----------------|------------|
| 22" | 24" | 22" | 24" |
| 42,5 – 47,5 cm | 44,5 – 49,5 cm | 44,5 – 49,5 cm | 47 – 52 cm |

Measurements

| Size | (a) Total length | (b) Total width ⁽¹⁾ | (c) Seat plate - back depth ⁽²⁾ | | Seat plate width | (d) Seat plate depth | |
|---------|------------------|--------------------------------|--|---------------------|------------------|----------------------|----------|
| | | | Standard seat plate | Extended seat plate | | Standard | Extended |
| Mini | 70 - 84 cm | 54 cm | 29,5 - 32,5 cm | 35 - 38 cm | 20,5 cm | 26,5 cm | 32 cm |
| 0 | 70 - 84 cm | 57 cm | 29,5 - 32,5 cm | 35 - 38 cm | 20,5 cm | 26,5 cm | 32 cm |
| 1 | 70 - 84 cm | 60 cm | 35 - 38 cm | 41 - 48 cm | 26,5 cm | 32 cm | 38 cm |
| 2 short | 70 - 84 cm | 63 cm | 35 - 38 cm | 41 - 48 cm | 26,5 cm | 32 cm | 38 cm |
| 2 long | 78 - 93 cm | 63 cm | 35 - 38 cm | 41 - 48 cm | 26,5 cm | 32 cm | 38 cm |
| 3 | 78 - 93 cm | 66 cm | 41 - 48 cm | 46 - 53 cm | 32,5 cm | 38 cm | 43 cm |
| 4 | 78 - 93 cm | 69 cm | 41 - 48 cm | 46 - 53 cm | 32,5 cm | 38 cm | 43 cm |
| 5 | 78 - 93 cm | 72 cm | 46 - 53 cm | — | 38,5 cm | 43 cm | — |
| 6 | 78 - 93 cm | 75 cm | 46 - 53 cm | — | 38,5 cm | 43 cm | — |

⁽¹⁾ The total width is reduced by 3 cm when applying a wheel camber of 0 degrees. ⁽²⁾ From the seat plate's front edge to the back

| Size | (e) Knee angle extension from seat plate | (g) Seat plate - back height | (h) Width between drive wheels ⁽³⁾ | | Frame length | (i) Inner frame width | Back recline |
|---------|--|------------------------------|---|-----------------|--------------|-----------------------|--------------|
| | | | Wheel guards incl. | No wheel guards | | | |
| Mini | bis 4 cm | 58 - 67 cm | 32,5 cm | 34,5 cm | 58 cm | 29,5 cm | 35° |
| 0 | bis 4 cm | 58 - 67 cm | 35,5 cm | 37,5 cm | 58 cm | 32,5 cm | 35° |
| 1 | bis 4 cm | 58 - 67 cm | 38,5 cm | 40,5 cm | 58 cm | 35,5 cm | 35° |
| 2 short | bis 6,5 cm | 58 - 67 cm | 41,5 cm | 43,5 cm | 58 cm | 38,5 cm | 35° |
| 2 long | bis 6,5 cm | 58 - 67 cm | 41,5 cm | 43,5 cm | 68 cm | 38,5 cm | 35° |
| 3 | bis 6,5 cm | 58 - 67 cm | 44,5 cm | 46,5 cm | 68 cm | 41,5 cm | 35° |
| 4 | bis 6,5 cm | 58 - 67 cm | 47,5 cm | 49,5 cm | 68 cm | 44,5 cm | 35° |
| 5 | bis 6,5 cm | 58 - 67 cm | 50,5 cm | 52,5 cm | 68 cm | 47,5 cm | 35° |
| 6 | bis 6,5 cm | 58 - 67 cm | 53,5 cm | 55,5 cm | 68 cm | 50,5 cm | 35° |

⁽³⁾ The distance between the drive wheels extends by 3 cm when applying a wheel camber of 0 degrees (referring to 22" drive wheels). Assuming 20" drive wheels, the distance between the drive wheels extends by 0.5 cm (3.5 cm in total) and assuming 24" drive wheels, the distance is reduced by 0.5 cm (2.5 cm in total).

Additional technical details available at www.rehatec.com -> Downloads. Or send us your request by email, fax or letter.

Valid from 01.01.2026 until recalled. © Unauthorized duplication without prior permission of Rehatec GmbH is strictly prohibited.

Technical changes reserved. Our general terms and conditions apply, see www.rehatec.com.

By ordering our products, you confirm that you have read and accepted our general terms and conditions

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, T: +49 6228 9136-0, F: +49 6228 9136-99, info@rehatec.com, www.rehatec.com

ATTENTION! Installation or retrofitting only possible by AAT!

| E-accessories | | | | | | | | | |
|--------------------|------|-----|-----|---------|--------|-----|-----|-----|-----|
| Power drives | Mini | 0 | 1 | 2 short | 2 long | 3 | 4 | 5 | 6 |
| V-MAX | X | X | X | WAK | WAK | WAK | WAK | WAK | WAK |
| V-MAX ² | X | X | X | WAK | WAK | WAK | WAK | WAK | WAK |
| MAX-E | X | X | X | WAK | WAK | WAK | WAK | WAK | WAK |
| s-max | X | X | X | VAK | VAK | VAK | VAK | VAK | VAK |
| CAMILINO | X | X | X | VAK | VAK | VAK | VAK | VAK | VAK |
| SOLO | VKR | VKR | VKR | VKR | VKR | VKR | VKR | VKR | VKR |
| SERVO | VKR | VKR | VKR | VKR | VKR | VKR | VKR | VKR | VKR |

The V-MAX mini push assist is not compatible with the Galileo seat shell mobility base!

X = Installation not possible; V = Installation possible with 24" W = Installation possible with 20" and 24";

R = Only Rehatec anti-tip devices possible; K = Installation possible with Kraftknotensystem; A = Only AAT anti-tip device possible

| Frame size / Compatibility | | | | | | | | | | | |
|----------------------------|----------|-----------|---------|-----------|---------|-----------|---------|-----------|---------|-----------|---------|
| | Mini/0/1 | 2K/2L | | 3 | | 4 | | 5 | | 6 | |
| Wheel size | 24" | 20" | 24" | 20" | 24" | 20" | 24" | 20" | 24" | 20" | 24" |
| V-MAX | X | V/O/K/R/A | | V/O/K/R/A | | V/O/K/R/A | | V/O/K/R/A | | V/O/K/R/A | |
| V-MAX ² | X | | | | | | | | | | |
| MAX-E | X | | | | | | | | | | |
| s-max | X | X | C/K/A/R | X | C/K/A/R | X | C/K/A/R | X | C/K/A/R | X | C/K/A/R |
| CAMILINO | X | X | C/K/A/R | X | C/K/A/R | X | C/K/A/R | X | C/K/A/R | X | C/K/A/R |
| SOLO | S/K/R/A | X | S/K/R/A | X | S/K/R/A | X | S/K/R/A | X | S/K/R/A | X | S/K/R/A |
| SERVO | S/K/R/A | X | S/K/R/A | X | S/K/R/A | X | S/K/R/A | X | S/K/R/A | X | S/K/R/A |

X = Installation not possible

0 = Installation only possible with 0° camber frame version

V = Overall length increases by 16 cm! Overall width increases by 4 cm! The distance between the drive wheels increases by 4 cm! The maximum seat depth corresponds to min. seat plate-back depth + 3 cm. Installation only possible with wheelbase extension (1021179), long brake handle (1015588) and widened parking brakes (1013170). These parts are only available from AAT!

C = Overall width increases by 3.5 cm! DThe maximum seat depth corresponds to min. seat plate-back depth + 3 cm! A seat pan tilt is not possible with this power drive! Installation only possible with wheel guard option (1017672 / 1017684)!

S = Overall width increases by 6 cm! The distance between the drive wheels increases by 3 cm! If wheel guards and anti-tip devices are required, installation only possible with wheelguard (1017672 / 1017684) and Rehatec anti-tip devices!

K = Rehatec Kraftknotensystem option possible

R = Rehatec anti-tip devices possible

A = AAT anti-tip devices possible

R = Rehatec anti-tip devices not possible!

A = AAT anti-tip devices not possible!

The Rehatec tipping bar and medical platform options are not possible with these power drives.

ATTENTION!

Planned combinations with power drives as well as with the s-max must be coordinated with AAT **before preparing the cost estimate! **

This overview has been prepared with the utmost care. Nevertheless, errors cannot be completely ruled out.

Rehatec® accepts no liability in such cases.

For further information, please contact AAT Antriebstechnik directly (www.aat-online.de).

Additional technical details available at www.rehatec.com -> Downloads. Or send us your request by email, fax or letter.

Valid from 01.01.2026 until recalled. © Unauthorized duplication without prior permission of Rehatec GmbH is strictly prohibited.

Technical changes reserved. Our general terms and conditions apply, see www.rehatec.com.

By ordering our products, you confirm that you have read and accepted our general terms and conditions

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, T: +49 6228 9136-0, F: +49 6228 9136-99, info@rehatec.com, www.rehatec.com

Compatible Electronic driving system

| Electronic driving system | Type <i>please specify</i> | Mini | 0 | 1 | 2 short | 2 long | 3 | 4 | 5 | 6 |
|-----------------------------------|-------------------------------|------|-----|---|---------|--------|---|---|---|---|
| scalamobil | S30 S35 | — | — | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
| viamobil | V15 V25 | — | — | — | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
| <i>Eco-Variation not possible</i> | | | | | | | | | | |
| scala- und viamobil | | — | — | — | — | — | — | ✓ | ✓ | ✓ |
| e-fix | E35 E36 | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
| e-motion | M15 | ✓ | M15 | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
| via GO ⁽¹⁾ | — | — | — | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |

Its not possible to assemble the tipping bar of Rehatec® for scalamobil and viamobil!

The assembly of the anti-tip-device for the wheelchair restrain system or the support loops of Rehatec® and the anti-tip-device of Alber is possible for every electronic driving system.

⁽¹⁾ The combination with the via GO push assist is generally possible from size 1 onwards!

For further details, please refer to the DIP (Dealer Information Pool) at <https://dip.alber.de/home.html>


scalamobil (S30/S35)

| Size | Seat plate – back depth (c) (page 2) | | Drive wheel size | User weight |
|---------|--------------------------------------|---------------------|----------------------|--------------------------|
| | Standard seat plate | Extended seat plate | | |
| Mini | — | — | — | — |
| 0 | — | — | — | — |
| 1 | 35 – 38 cm | 41 – 45 cm | 12" + 16", 20" – 24" | bis 60 kg |
| 2 short | 35 – 38 cm | 41 – 45 cm | 12" + 16", 20" – 24" | bis 60 kg |
| 2 long | 35 – 38 cm | 41 – 45 cm | 12" + 16", 20" – 24" | bis 60 kg |
| 3 | 41 – 45 cm | 46 – 50 cm | 12" + 16", 20" – 24" | bis 60 kg |
| 4 | 41 – 45 cm | 46 – 50 cm | 12" + 16", 20" – 24" | bis 90 kg ⁽²⁾ |
| 5 | 46 – 50 cm | — | 12" + 16", 20" – 24" | bis 120 kg |
| 6 | 46 – 50 cm | — | 12" + 16", 20" – 24" | bis 120 kg |

When configuring a Galileo size 1–3 with Scalamobil and Kraftknottensystem, the seat tilt is limited (maximum 18° possible).

With 16" wheels and Scalamobil, the Kraftknottensystem is not possible!

Only from 20" possible!




⁽²⁾ Mit doppelter Gasdruckfeder bis zu 120 kg

viamobil (V15/V25)


| Size | Seat plate – back depth (c) (page 2) | | Drive wheel size |
|---------|--------------------------------------|---------------------|----------------------|
| | Standard seat plate | Extended seat plate | |
| Mini | — | — | — |
| 0 | — | — | — |
| 1 | — | — | — |
| 2 short | 35 – 38 cm | 41 – 45 cm | 12" + 16", 20" – 24" |
| 2 long | 35 – 38 cm | 41 – 45 cm | 12" + 16", 20" – 24" |
| 3 | 41 – 45 cm | 46 – 50 cm | 12" + 16", 20" – 24" |
| 4 | 41 – 45 cm | 46 – 50 cm | 12" + 16", 20" – 24" |
| 5 | 46 – 50 cm | — | 12" + 16", 20" – 24" |
| 6 | 46 – 50 cm | — | 12" + 16", 20" – 24" |

ATTENTION!
The seat tilt is only possible up to a maximum of 10° as standard! Drive wheels only available from 20"!




e-Fix (E35 / E36)

| Size | Seat plate – back depth (c) (page 2) | | Drive wheel size | Total width | Width between drive wheels (h) | |
|---------|--------------------------------------|---------------------|------------------|-------------|--------------------------------|---------------------|
| | Standard seat plate | Extended seat plate | | | with wheel guard | without wheel guard |
| Mini | 29,5 – 32,5 cm | 35 – 38 cm | 22" – 24" | 54 cm | 31 cm | 33 cm |
| 0 | 29,5 – 32,5 cm | 35 – 38 cm | 22" – 24" | 57 cm | 33 cm | 36 cm |
| 1 | 35 – 38 cm | 41 – 48 cm | 22" – 24" | 60 cm | 37 cm | 39 cm |
| 2 short | 35 – 38 cm | 41 – 48 cm | 22" – 24" | 63 cm | 40 cm | 42 cm |
| 2 long | 35 – 38 cm | 41 – 48 cm | 22" – 24" | 63 cm | 40 cm | 42 cm |
| 3 | 41 – 48 cm | 46 – 53 cm | 22" – 24" | 66 cm | 43 cm | 45 cm |
| 4 | 41 – 48 cm | 46 – 53 cm | 22" – 24" | 69 cm | 46 cm | 48 cm |
| 5 | 46 – 53 cm | — | 22" – 24" | 72 cm | 49 cm | 51 cm |
| 6 | 46 – 53 cm | — | 22" – 24" | 75 cm | 52 cm | 54 cm |



e-motion (M15)

| Size | Seat plate – back depth (c) (page 2) | | Drive wheel size | Total width |
|---------|--------------------------------------|---------------------|------------------|-------------|
| | Standard seat plate | Extended seat plate | | |
| Mini | 29,5 – 32,5 cm | 35 – 38 cm | 22" – 24" | 54 cm |
| 0 | 29,5 – 32,5 cm | 35 – 38 cm | 22" – 24" | 57 cm |
| 1 | 35 – 38 cm | 41 – 48 cm | 22" – 24" | 60 cm |
| 2 short | 35 – 38 cm | 41 – 48 cm | 22" – 24" | 63 cm |
| 2 long | 35 – 38 cm | 41 – 48 cm | 22" – 24" | 63 cm |
| 3 | 41 – 48 cm | 46 – 53 cm | 22" – 24" | 66 cm |
| 4 | 41 – 48 cm | 46 – 53 cm | 22" – 24" | 69 cm |
| 5 | 46 – 53 cm | — | 22" – 24" | 72 cm |
| 6 | 46 – 53 cm | — | 22" – 24" | 75 cm |




Additional technical details available at www.rehatec.com -> Downloads. Or send us your request by email, fax or letter.

Valid from 01.01.2026 until recalled. © Unauthorized duplication without prior permission of Rehatec GmbH is strictly prohibited.

Technical changes reserved. Our general terms and conditions apply, see www.rehatec.com.

By ordering our products, you confirm that you have read and accepted our general terms and conditions

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, T: +49 6228 9136-0, F: +49 6228 9136-99, info@rehatec.com, www.rehatec.com



| Push assist EMPULSE R20 | | | | | | | |
|-------------------------|-------|--|------------|------------|--|------------|------------|
| Size | Zeile | Possible position for wheel axle when clamps are mounted on the frame (P1) | | | Possible position for wheel axle when clamps are mounted on the frame (P2) | | |
| | | 20 inch | 22 inch | 24 inch | 20 inch | 22 inch | 24 inch |
| Mini | A | — | — | — | — | — | — |
| | B | | | | | | |
| | C | | | | | | |
| 0 | A | 1, 2, 3, 4, 5 | — | 2, 3, 4, 5 | — | — | — |
| | B | | | | | | |
| | C | | | | | | |
| 1 | A | 1, 2, 3, 4, 5 | — | 2, 3, 4, 5 | — | — | — |
| | B | | | | | | |
| | C | | | | | | |
| 2 | A | — | — | 2, 3, 4, 5 | — | 1, 2, 3 | 1, 2, 3 |
| | B | | | | | 1, 2, 3 | 1, 2, 3 |
| | C | | | | | 1, 2, 3 | 1, 2, 3 |
| 3 | A | — | — | — | 1, 2, 3 | 1, 2, 3 | 1, 2, 3 |
| | B | — | 2, 3, 4, 5 | 2, 3, 4, 5 | 1, 2, 3 | 1, 2, 3 | 1, 2, 3 |
| | C | 2, 3, 4, 5 | 2, 3, 4, 5 | 2, 3, 4, 5 | 1, 2, 3 | 1, 2, 3 | 1, 2, 3 |
| 4 | A | — | — | — | 1, 2 | 1, 2, 3 | 1, 2, 3, 4 |
| | B | | — | 3, 4, 5 | 1, 2, 3 | 1, 2, 3, 4 | 1-5 |
| | C | | 3, 4, 5 | 3, 4, 5 | 1, 2, 3, 4 | 1-5 | 1, 2, 3, 4 |
| 5 | A | — | — | 1, 2, 3 | 1-5 | — | 1, 2, 3, 4 |
| | B | — | 3, 4, 5 | 1, 2, 3 | 1, 2, 3, 4 | 1, 2, 3, 4 | 1, 2, 3, 4 |
| | C | 3, 4, 5 | 3, 4, 5 | 1, 2, 3 | 1, 2, 3, 4 | 1, 2, 3, 4 | 1, 2, 3, 4 |
| 6 | A | — | — | 1, 2, 3 | 1-5 | — | 1, 2, 3, 4 |
| | B | — | 3, 4, 5 | 1, 2, 3 | 1, 2, 3, 4 | 1, 2, 3, 4 | 1, 2, 3, 4 |
| | C | 3, 4, 5 | 3, 4, 5 | 1, 2, 3 | 1, 2, 3, 4 | 1, 2, 3, 4 | 1, 2, 3, 4 |



This overview has been prepared with the utmost care.
Nevertheless, errors cannot be completely ruled out.
Rehatec® accepts no liability in such cases.
For further information, please contact Sunrise Medical directly
(www.sunrisemedical.de)

Base frame

Galileo Mobility Base for e-driving systems

REHATEC®

CAUTION! Please consider wheel camber!

| Standard frame, abducted | | | | 2° wheel camber | Closed frame, abducted | | | | | | | | | | | |
|---|--------------------------|--|-------------------|---|------------------------|--|-------------------|--|--|--|------------|------------|--------------------|--------------------------|------------------------|--------------------------|
| Single gas spring Total load up to 79s kg | | Double gas spring Total load up to 79 kg | | Double gas spring Total load up to 79 kg | | Double gas spring (required when 80 kg are exceeded!) Total load up to 120 kg | | | | | | | | | | |
| Size Mini | (1015911) | Size 3 | (1015917) | Size 2 long | (1017182) | Size 3 | (1017253) | | | | | | | | | |
| Size 0 | (1015912) | Size 4 | (1015918) | Size 3 | (1017251) | Size 4 | (1017254) | | | | | | | | | |
| Size 1 | (1015913) | Size 5 | (1015827) | Size 4 | (1017252) | Size 5 | (1017255) | | | | | | | | | |
| Size 2 short | (1015810) | Closed frame with double gas spring required from 80 kg upwards! Specify total load! | | Closed frame with double gas spring required from 80 kg upwards! Specify total load! | | Size 6 | (1017800) | | | | | | | | | |
| Size 2 long | (1015919) | | | | | | | | | | | | | | | |
| Size 3 | (1015920) | | | | | | | | | | | | | | | |
| Size 4 | (1016462) | | | | | | | | | | | | | | | |
| | | <table><tr><td>Total load</td><td>Gas spring</td></tr><tr><td>up to 79 kg</td><td>2 × 200 N</td></tr></table> | Total load | Gas spring | up to 79 kg | 2 × 200 N | | | <table><tr><td>Total load</td><td>Gas spring</td></tr><tr><td>up to 79 kg</td><td>2 × 200 N ⁽¹⁾</td></tr><tr><td>exceeding 80 kg</td><td>2 × 350 N ⁽¹⁾</td></tr></table> | | Total load | Gas spring | up to 79 kg | 2 × 200 N ⁽¹⁾ | exceeding 80 kg | 2 × 350 N ⁽¹⁾ |
| Total load | Gas spring | | | | | | | | | | | | | | | |
| up to 79 kg | 2 × 200 N | | | | | | | | | | | | | | | |
| Total load | Gas spring | | | | | | | | | | | | | | | |
| up to 79 kg | 2 × 200 N ⁽¹⁾ | | | | | | | | | | | | | | | |
| exceeding 80 kg | 2 × 350 N ⁽¹⁾ | | | | | | | | | | | | | | | |
| Base price | 2.867, – € | Base price | 3.326, – € | Base price | 3.293, – € | Base price | 3.699, – € | | | | | | | | | |

⁽¹⁾ In case you do not specify the total load, we apply 2 × 200 N by default.

| Standard frame, abducted | | | | 0° wheel camber | Closed frame, abducted | | | | | | | | | | | | |
|--|--------------------------|---|-------------------|---|------------------------|--|-------------------|--|--|--|------------|------------|-------------|--------------------------|-----------------|--------------------------|--|
| Single gas spring Total load up to 79 kg | | Double gas spring Total load up to 79 kg | | Double gas spring Total load up to 79 kg | | Double gas spring (required when 80 kg are exceeded!) Total load up to 120 kg | | | | | | | | | | | |
| Size Mini (1018668) | | Size 3 (1018675) | | Size 2 long(1018683) | | Size 3 (1018686) | | | | | | | | | | | |
| Size 0 (1018669) | | Size 4 (1018676) | | Size 3 (1018684) | | Size 4 (1018687) | | | | | | | | | | | |
| Size 1 (1018670) | | Size 5 (1018677) | | Size 4 (1018685) | | Size 5 (1018688) | | | | | | | | | | | |
| Size 2 short (1018671) | | Closed frame with double gas spring required from 80 kg upwards! Specify total load! | | Closed frame with double gas spring required from 80 kg upwards! Specify total load! | | Size 6 (1018689) | | | | | | | | | | | |
| Size 2 long (1018672) | | | | | | | | | | | | | | | | | |
| Size 3 (1018673) | | | | | | | | | | | | | | | | | |
| Size 4 (1018674) | | | | | | | | | | | | | | | | | |
| | | <table><tr><td>Total load</td><td>Gas spring</td></tr><tr><td>up to 79 kg</td><td>2 × 200 N</td></tr></table> | Total load | Gas spring | up to 79 kg | 2 × 200 N | | | | <table><tr><td>Total load</td><td>Gas spring</td></tr><tr><td>up to 79 kg</td><td>2 × 200 N ⁽¹⁾</td></tr><tr><td>exceeding 80 kg</td><td>2 × 350 N ⁽¹⁾</td></tr></table> | Total load | Gas spring | up to 79 kg | 2 × 200 N ⁽¹⁾ | exceeding 80 kg | 2 × 350 N ⁽¹⁾ | |
| Total load | Gas spring | | | | | | | | | | | | | | | | |
| up to 79 kg | 2 × 200 N | | | | | | | | | | | | | | | | |
| Total load | Gas spring | | | | | | | | | | | | | | | | |
| up to 79 kg | 2 × 200 N ⁽¹⁾ | | | | | | | | | | | | | | | | |
| exceeding 80 kg | 2 × 350 N ⁽¹⁾ | | | | | | | | | | | | | | | | |
| Base price | 2.867, – € | Base price | 3.326, – € | Base price | 3.293, – € | Base price | 3.699, – € | | | | | | | | | | |

⁽¹⁾ In case you do not specify the total load, we apply 2 × 200 N by default.

Frame colours

| | | |
|---|---|---|
|  Pure white (RAL 9010) |  Bordeaux violet (RAL 4004) |  Luminous green (RAL 6038) |
|  Daffodil yellow (RAL 1007) |  Ultramarine blue (RAL 5002) |  Anthracite grey, matt (RAL 7016m) |
|  Luminous yellow (RAL 1026) |  Metallic traffic blue* |  Metallic silver* |
|  Pure orange (RAL 2004) |  Pearl night blue, matt (RAL 5026) |  Metallic anthracite* |
|  Luminous orange (RAL 2005) |  Water blue (RAL 5021) |  Graphite black, matt (RAL 9011m) |
|  Ruby red (RAL 3003) |  Light green (RAL 6027) |  Glossy jet black (RAL 9005g) |
|  Pearl ruby red, matt (RAL 3032) |  Yellow green (RAL 6018) | |
|  Heather violet (RAL 4003) |  Pearl green, matt (RAL 6035) | |

* keine RAL Farben

This is only an overview of colours. Find all details at www.rehatec.com.

Patient's muscle tone

Stereotypic movements
(e.g. permanent body rocking)*

Measurements

| Seath shell width | Seat shell depth |
|-------------------|------------------|
| cm | cm |

Total load (patient+seat shell)

kg

* Please check whether any customisations, such as reinforcements of the base frame, are required due to stereotypical behaviour! Requirements can be specified under "Notes" on the last page!

Additional technical details available at www.rehatec.com -> Downloads. Or send us your request by email, fax or letter.

Valid from 01.01.2026 until recalled. © Unauthorized duplication without prior permission of Rehatec GmbH is strictly prohibited.

Technical changes reserved. Our general terms and conditions apply, see www.rehatec.com.





By ordering our products, you confirm that you have read and accepted our general terms and conditions

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, T: +49 6228 9136-0, F: +49 6228 9136-99, info@rehatec.com, www.rehatec.com

Wheels, backrest and armrests

REHATEC®


Galileo Mobility Base for e-driving systems


| Drive wheels including drum brake | | | | | | | | | | | | |
|--|-------|--|-----|-----|-----|-----|--|--|---|--|---|-----|
| <div>Caution!</div> <div>Mountainbike and Big Apple wheels extend Galileo's total width by 4 cm!</div> | | <div>Standard version</div> <div></div> | | | | | <div>Mountainbike</div> <div>Code 1027864</div> <div>Off-road tyres</div> <div></div> | | <div>Big Apple</div> <div>Code 1027862</div> <div>Only possible with spoke guard 22"</div> <div></div> | | <div>Marathon</div> <div>Code 10278875 (22")</div> <div>Code 1027861 (24")</div> <div>Thin tyres, shallow tyre tread</div> <div></div> | |
| | | Pair | | | | | Pair 369, – € | | Pair 369, – € | | Pair/extra charge 86, – € | |
| | | 12" | 16" | 20" | 22" | 24" | 24" | | 24" | | 22" | 24" |
| Solid rubber | Grey | — | — | | | | — | | — | | — | |
| | Black | | — | | | | — | | — | | — | |
| Pneumatic | Grey | — | — | | | | — | | — | | — | |
| | Black | | | | | | | | | | | |



| Possible combinations | | | | | |
|-----------------------|-------|-----|-------|-----|-----|
| | 12" | 16" | 20" | 22" | 24" |
| 5" | ✓ | ✓ | ✓ | ✓ | ✓ |
| 6" | ✓ | ✓ | ✓ | ✓ | ✓ |
| 7" | ✓ | ✓ | ✓ | ✓ | ✓ |
| 8" | ⚠ (4) | ✓ | ⚠ (4) | ✓ | ✓ |



(4) Only in combination with width extension kit for drive wheels (Diagonal version: seat height reduced by 4 cm (1010879)).



| Castor wheels | | | | | |
|---------------|-------|----|----|----|----|
| | | 5" | 6" | 7" | 8" |
| Solid rubber | Grey | | | | |
| | Black | | | | |
| Pneumatic | Grey | — | | | |
| | Black | — | | | |

| Push bar | |
|--|----------|
| Push bar, height- and angle-adjustable Code 1024683  | |
| Stück | 170, – € |

| Push rims | | |
|--|---------|----------------------------|
| Push rims, anodised aluminium Sturdy, high-quality push rims, width-adjustable | | |
|  | | |
| Only compatible with standard rims (pneumatic, solid rubber, and Marathon tyres)! | | |
| Size | colour | Code |
| 20" | black | 1025482-S |
| 22" | silver | 1025388-N |
| 24" | black | 1025389-S |
| Mounting: | | tight (standard) wide |
| Paar | 80, – € | |

| Configuration | | Colour of the back | Brake handle locking | Tilt-in-space | Seat plate |
|--|--|--|----------------------|---------------|------------|
| Mounting of the parking brake | | Standard | Standard | Standard | Standard |
|  Graphite black, matt | |  Graphite black, matt | Automatic | 0° to 40° | Standard |
| | | | optional | optional | optional |
| | | | Manual | -5° to 35° | Extended |

| Back | |
|---|----------|
| Back fastening with split, fixed bracket Code 1016485  | |
| Not to be combined with back element! | |
| Each | 290, – € |
| Back fastening with split, adjustable bracket Code 1017928  | |
| Not to be combined with back element! For perfect guidance of the back section | |
| Each | 327 – € |

| Arm rests | | | | | | | | | | | | | | | | | | | | | | | |
|---|------------------------------------|---|---|-------------------|------------------------------------|---|---|------|------------------------------------|--------|------------|-----|------------|-----|------------|-----|------------|---|--|-----------------|-------|-------|-------|
| Arm rests, standard Code 1017771 | | | Arm rests, comfort Code 1017437 | | | | | | | | | | | | | | | | | | | | |
| Toothed segments make them adjustable in height, width and angle | | | Clamping system makes them adjustable in height, width and angle Backwards foldable by 95° | | | | | | | | | | | | | | | | | | | | |
| <table><tr><td>(a) Pipe length</td></tr><tr><td>23 cm</td></tr><tr><td>28 cm</td></tr><tr><td>33 cm</td></tr></table> | | (a) Pipe length | 23 cm | 28 cm | 33 cm |  | <table><tr><th>Size</th><th>(b) Distance between the arm rests</th></tr><tr><td>Mini/0</td><td>19 - 35 cm</td></tr><tr><td>1/2</td><td>24 - 39 cm</td></tr><tr><td>3/4</td><td>30 - 45 cm</td></tr><tr><td>5/6</td><td>36 - 51 cm</td></tr></table> | Size | (b) Distance between the arm rests | Mini/0 | 19 - 35 cm | 1/2 | 24 - 39 cm | 3/4 | 30 - 45 cm | 5/6 | 36 - 51 cm | <table><tr><td>(a) Pipe length</td></tr><tr><td>29 cm</td></tr><tr><td>34 cm</td></tr><tr><td>39 cm</td></tr></table> | | (a) Pipe length | 29 cm | 34 cm | 39 cm |
| (a) Pipe length | | | | | | | | | | | | | | | | | | | | | | | |
| 23 cm | | | | | | | | | | | | | | | | | | | | | | | |
| 28 cm | | | | | | | | | | | | | | | | | | | | | | | |
| 33 cm | | | | | | | | | | | | | | | | | | | | | | | |
| Size | (b) Distance between the arm rests | | | | | | | | | | | | | | | | | | | | | | |
| Mini/0 | 19 - 35 cm | | | | | | | | | | | | | | | | | | | | | | |
| 1/2 | 24 - 39 cm | | | | | | | | | | | | | | | | | | | | | | |
| 3/4 | 30 - 45 cm | | | | | | | | | | | | | | | | | | | | | | |
| 5/6 | 36 - 51 cm | | | | | | | | | | | | | | | | | | | | | | |
| (a) Pipe length | | | | | | | | | | | | | | | | | | | | | | | |
| 29 cm | | | | | | | | | | | | | | | | | | | | | | | |
| 34 cm | | | | | | | | | | | | | | | | | | | | | | | |
| 39 cm | | | | | | | | | | | | | | | | | | | | | | | |
|  | | <table><tr><th>Size</th><th>(b) Distance between the arm rests</th></tr><tr><td>Mini/0</td><td>25 - 42 cm</td></tr><tr><td>1/2</td><td>31 - 46 cm</td></tr><tr><td>3/4</td><td>37 - 52 cm</td></tr><tr><td>5/6</td><td>43 - 58 cm</td></tr></table> | | Size | (b) Distance between the arm rests | Mini/0 | 25 - 42 cm | 1/2 | 31 - 46 cm | 3/4 | 37 - 52 cm | 5/6 | 43 - 58 cm | | | | | | | | | | |
| Size | (b) Distance between the arm rests | | | | | | | | | | | | | | | | | | | | | | |
| Mini/0 | 25 - 42 cm | | | | | | | | | | | | | | | | | | | | | | |
| 1/2 | 31 - 46 cm | | | | | | | | | | | | | | | | | | | | | | |
| 3/4 | 37 - 52 cm | | | | | | | | | | | | | | | | | | | | | | |
| 5/6 | 43 - 58 cm | | | | | | | | | | | | | | | | | | | | | | |
| Paar | Please select one | 350, – € | Paar | Please select one | 513, – € | | | | | | | | | | | | | | | | | | |

Additional technical details available at www.rehatec.com -> Downloads. Or send us your request by email, fax or letter.

Valid from 01.01.2026 until recalled. © Unauthorized duplication without prior permission of Rehatec GmbH is strictly prohibited.

Technical changes reserved. Our general terms and conditions apply, see www.rehatec.com.

By ordering our products, you confirm that you have read and accepted our general terms and conditions

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, T: +49 6228 9136-0, F: +49 6228 9136-99, info@rehatec.com, www.rehatec.com

Frames, adapters and safety

REHATEC®


Galileo Mobility Base for e-driving systems

Frame

Wheel base extension

Code 1021179

Extended
by 6 to 11 cm



Not to be combined with scala-/viamobil, 12/16" wheels, tipping bar, tipping bar for vent tray or the extension kit for drive wheels!

Pair

442, – €

Die Halterungen für e-fix und e-motion, sowie sämtliches weiteres Zubehör (Bolzen, etc.) für deinen E-Antrieb musst du selbst bei der Alber GmbH bestellen.



Bracket for scala / viamobil

| | scalamobil Code | | |
|------|-----------------|---------|---------|
| Size | 12" | 16" | 20-24" |
| 1 | 1457771 | 1594502 | 1591745 |
| 2k | | | |
| 2l | | | |
| 3 | | | |
| 4 | 1592724 | | 1591770 |
| 5 | | | |
| 6 | | | |

| viamobil Code | | | |
|---------------|---------|-----|---------|
| Size | 12" | 16" | 20-24" |
| 1 | - | - | - |
| 2k | 1592713 | | 1591742 |
| 2l | | | |
| 3 | 1592723 | | 1591746 |
| 4 | 1592724 | | 1591770 |
| 5 | | | |
| 6 | | | |

Mounting of the Scala/Viamobil bracket by REHATEC®

Code 4005

Not eligible for discount!

Each

362, – €

Each

89, – €

Seat shell adapter



Trapezoidal adapter, complete⁽²⁾

Gr. 1-6

Gr. Mini-0


| For size | Code | a | b |
|----------|---------|-------|-------|
| Mini-0 | 1020031 | 20 cm | 21 cm |

| For size | Code | c | d |
|----------|---------|-------|-------|
| 1-2 | 1008603 | 24 cm | 25 cm |
| 3-6 | 1008589 | 30 cm | 28 cm |



⁽²⁾ Sizes Mini and 0 include pin instead of lever.

Trapezoidal adapter, lower part



| For size | Code | a | b |
|----------|---------|-------|-------|
| Mini-0 | 1016878 | 20 cm | 21 cm |
| 1-2 | 1011358 | 24 cm | 25 cm |
| 3-6 | 1011356 | 30 cm | 28 cm |

Each

438, – €


Each

230, – €

Safety

Tipping bar

Code 1003725




Not possible with scala / viamobil.

Left
Right

93, – €
93, – €

Anti-tip

Code 1016245




Left
Right

161, – €
161, – €

Scalamobil anti-tip device without lifting function with 12 mm mount

Code 341-A



Only possible in combination with scala / viamobil bracket! Not eligible for discount!

Pair (customisation)

865, – €

Additional technical details available at www.rehatec.com -> Downloads. Or send us your request by email, fax or letter.

Valid from 01.01.2026 until recalled. © Unauthorized duplication without prior permission of Rehatec GmbH is strictly prohibited.

Technical changes reserved. Our general terms and conditions apply, see www.rehatec.com.

By ordering our products, you confirm that you have read and accepted our general terms and conditions

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, T: +49 6228 9136-0, F: +49 6228 9136-99, info@rehatec.com, www.rehatec.com

Swing-up Leg Positioning

REHATEC®

Galileo Mobility Base for e-driving systems

Swing-up foot supports, standard

Swing-up parted foot rests, standard


Code 1019503

Adjustable in width and depth

Swing-away, removable and (mechanical) swing-up foot rests

Foot rest mounting incl.

Only optional height adjustment for the foot rest enables the adjustment of the height of physiological pivot point.



Available for Galileo size 2 and bigger!


| a (leg length) | b (knee angle) | c (pivot point - seat plate distance) |
|----------------|----------------|---------------------------------------|
| 36–58 cm | 85° | 11 cm |

Footplate, plastic

Code 1019439

Parted swing-up foot rest, angle-adjustable by 360°

| For size | a | b |
|----------|-------|---------|
| 2 | 16 cm | 14 cm |
| 3–4 | 16 cm | 16 cm |
| 5–6 | 16 cm | 18,5 cm |



Base price

557, – €


Accessories for swing-up foot supports, standard

Footplate, aluminium

Code 1018565

Parted swing-up foot rest, angle-adjustable by 360°

| For size | a | b |
|----------|-------|---------|
| 2 | 16 cm | 13,5 cm |
| 3 | 16 cm | 15 cm |
| 4 | 24 cm | 16,5 cm |
| 5+6 | 24 cm | 18 cm |
| 5+6 | 24 cm | 21 cm |



Footplates 24x21 cm only available from a seat shell width of 47 cm!


Pair

191, – €

Foot rest height adjustment

Code 1017760

To adjust the physiological pivot point



Pair


118, – €

Swing-away calf support

Code 1019467

Vertically adjustable, adapts to the user's calf

| For size | a | b |
|----------|-------|-------|
| 2–3 | 15 cm | 12 cm |
| 4–6 | 21 cm | 15 cm |




Pair

158, – €

Heel support

Code 1019442

Mounted on plastic footplate. Enclosed when you order aluminium foot rests.



Pair

78, – €

Swing-up foot supports, special

Swing-up parted foot rests, special


Code 1018558

Adjustable in width, depth and height (foot rest height adjustment)

Swing-away, removable and swing-up (via gas spring)

Foot rest mounting incl.

Adjustable physiological pivot point




Available for Galileo size 2 and bigger! Intended for spastic users!

| a (Leg length) | b (Knee angle) | c (pivot point - seat plate distance) |
|----------------|----------------|---------------------------------------|
| 36–58 cm | 80° | 15,5–25,5 cm |

Footplate, plastic

Code 1019439

Parted swing-up foot rest, angle-adjustable by 360°




| For size | a | b |
|----------|-------|---------|
| 2 | 16 cm | 14 cm |
| 3+4 | 16 cm | 16 cm |
| 5+6 | 16 cm | 18,5 cm |

Footplate, aluminium

Code 1018565

Parted swing-up foot rest, angle-adjustable by 360°



| For size | a | b |
|----------|-------|---------|
| 2 | 16 cm | 13,5 cm |
| 3 | 16 cm | 15 cm |
| 4 | 24 cm | 16,5 cm |
| 5+6 | 24 cm | 18 cm |
| 5+6 | 24 cm | 21 cm |

Footplates 24x21 cm only available from a seat shell width of 47 cm!


Plastic

Aluminium^(*)

Foot rest height adjustment

Code 1017760

To adjust the physiological pivot point




Swing-away calf support

Code 1019467

Vertically adjustable, adapts to the user's calf

| For size | a | b |
|----------|-------|-------|
| 2–3 | 15 cm | 12 cm |
| 4–6 | 21 cm | 15 cm |



Base price (Pair, customisation)


994, – €

Accessories for swing-up foot supports, special

Heel support

Code 1019442

Mounted on plastic footplate. Enclosed when you order aluminium footplate.



Pair

78, – €

^(*) If nothing is selected, this option will be supplied.

Additional technical details available at www.rehatec.com -> Downloads. Or send us your request by email, fax or letter.

Valid from 01.01.2026 until recalled. © Unauthorized duplication without prior permission of Rehatec GmbH is strictly prohibited.

Technical changes reserved. Our general terms and conditions apply, see www.rehatec.com.

By ordering our products, you confirm that you have read and accepted our general terms and conditions


Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, T: +49 6228 9136-0, F: +49 6228 9136-99, info@rehatec.com, www.rehatec.com

Leg positioning

Continuous, light-weight footplate

Fixed knee angle with footplate mounting

Aluminium knee angle and footplate



Only for size Mini to size 2!


19 cm deep (Code 1016648)

268, – €

Continuous footplate

Adjustable knee angle, fixed foot angle with footplate mounting

Steel knee angle, aluminium footplate



Footplate only available for size 1 and bigger! Depth of 24 cm only available for size 2 and bigger!


16 cm deep, for size 1 and bigger (Code 213)
24 cm deep, for size 2 and bigger (Code 213.24)

336, – €

388, – €

Footplate, parted

Adjustable knee angle, fixed foot angle with mounting. Knee angle made of steel, footboard made of aluminium.



Footplate only available for size 1 and bigger! Depth of 24 cm only available for size 2 and bigger!


16 cm deep, for size 1 and bigger (Code 21301)

24 cm deep, for size 2 and bigger (Code 21301.24)

415, – €

468, – €

Footplate mounting for footplates of other companies




| Code | for Size | |
|---------|----------|--|
| 1007282 | Mini – 0 | 15 x 15 mm |
| 1011252 | 1 – 6 | 20x20 mm square incl. inlay for 15x15 mm square tube |

Pair

124, – €

Adjustable foot angle

Code 214




Not to be combined with folding mechanism and light-weight footplate.

Pair/ Extra charge

121, – €

Folding mechanism -22° up to 90°

Code 1017724




Not to be combined with adjustable foot angle and light-weight footplate

Pair/ Extra charge

189, – €

Heel support

Not to be combined with light-weight footplate.



| Code | Footplate | Quantity |
|-------|--------------------------|----------|
| 217-1 | for continuous footplate | Piece |
| 217-2 | for parted footplate | Pair |


Piece/ Pair

121, – €

Calf support, continuous

Not available for lightweight footboard.

| Code | For size | a | b |
|---------|----------|-------|-------|
| 1010801 | | 11 cm | 28 cm |
| 1010802 | 1 – 6 | 11 cm | 31 cm |
| 1010803 | | 16 cm | 33 cm |
| 1010804 | 2 – 6 | 16 cm | 36 cm |
| 1010805 | 4 – 6 | 16 cm | 39 cm |




Each

206, – €

Calf supports, parted

Not available for light-weight footboard.

| Code | For size | a | b | c |
|---------|----------|-------|---------|---------|
| 1010835 | 1 – 6 | 11 cm | 12,5 cm | 26,5 cm |
| 1010837 | | 11 cm | 15 cm | 31 cm |
| 1010314 | 2 – 6 | 16 cm | 18 cm | 37,5 cm |



Pair

256, – €

Additional technical details available at www.rehatec.com -> Downloads. Or send us your request by email, fax or letter.

Valid from 01.01.2026 until recalled. © Unauthorized duplication without prior permission of Rehatec GmbH is strictly prohibited.

Technical changes reserved. Our general terms and conditions apply, see www.rehatec.com.

By ordering our products, you confirm that you have read and accepted our general terms and conditions

Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, T: +49 6228 9136-0, F: +49 6228 9136-99, info@rehatec.com, www.rehatec.com

Seating system


Seat element without connecting hinge

Code 1017923

Colour: graphite black, matt (RAL 9011m)

Not to be combined with trapezoidal adapter!

| Size | a (depth) | b (width) |
|------|-----------|-----------|
| Mini | 34–39 cm | 25–30 cm |
| 0 | 34–38 cm | 28–30 cm |
| 1 | 34–38 cm | 31–36 cm |
| 2 | 40–47 cm | 34–39 cm |
| 3 | 40–47 cm | 37–43 cm |
| 4 | 45–53 cm | 40–46 cm |
| 5 | 45–53 cm | 43–50 cm |




Back element without connecting hinge

Code 1017924

Colour: graphite black, matt (RAL 9011m)

| For size | a (back height) | | b (width) | |
|----------|-----------------|-------|-----------|-------|
| Mini | 35 cm | 40 cm | | 26 cm |
| 0 | 35 cm | 40 cm | 45 cm | 29 cm |
| 1 | 40 cm | 45 cm | 50 cm | 32 cm |
| 2 | 45 cm | 50 cm | 55 cm | 35 cm |
| 3 | 45 cm | 50 cm | 55 cm | 38 cm |
| 4 | 50 cm | 55 cm | 60 cm | 41 cm |
| 5 | 50 cm | 55 cm | 60 cm | 44 cm |



Not to be combined with back fastening systems for seat shells!

Each

237, – €


Each

388, – €

Connecting hinge


Code 1017925

To stabilise the seat element and back element, abducted.
To be combined with seat element and back element.



Pair

Seat element extension towards the back



| Size | Code |
|--------|---------|
| Mini–0 | 1018300 |
| 1–2I | 1018297 |
| 3–4 | 1018301 |
| 5 | 1018302 |


Each

Sitzsystem

Universal bracket to mount the head support at the back

Code 1009420


In case you do not order any back element, we enclose this bracket



Head support, shell shaped

Code 60013

| Size | a | b |
|------|-------|-------|
| 0 | 13 cm | 22 cm |
| 1 | 16 cm | 28 cm |
| 2 | 20 cm | 33 cm |
| 3 | 23 cm | 38 cm |



Each

50, – €

Each

259, – €

Galileo Mobility Base for e-driving systems

For any customisations, please use the 'Modifications/Customisations' form sheet available at www.rehatec.com under 'Downloads'.

Please consider that the prices of spare parts might differ from the prices specified in this order form.

Valid from 01.01.2026 until recalled. © Unauthorized duplication without prior permission of Rehatec GmbH is strictly prohibited.

By ordering our products, you confirm that you have read and accepted our general terms and conditions

By ordering our products, you confirm that you have read and accepted our general terms and conditions
Rehatec® GmbH, In den Kreuzwiesen 35, 69250 Schönau, **T: +49 6228 9136-0, F: +49 6228 9136-99**, info@rehatec.com, www.rehatec.com